FV200 Series



Max. speed: 0 rpm Stitch length adjustment: Lever Diff. feed ratio adjustment: Lever

Subclass						
Fabric thickness	Subclasses	Number of needles	Number of threads	Needle space	Seam width	
~	FV203- 02BA	3	6	6.4 · 7.2mm	-	
~	FV205- 02BA	3	6	6.4 · 7.2mm	121	
~	FV205- 02CA	3	6	6.4 · 7.2mm	(=1	

The feed-off-the-arm cylinder bed is the most suitable for lap seaming operations on cylindrical goods such as side seaming or inseaming on Jeans of Work pants, side seaming or sleeve seaming on Denim jackets, providing easy lap seaming and eliminating the need for sophisticated techniques, so that even unskilled operator can use the machine.

Knurled roller prevents plyshift

The knurled roller located at the end of the cylinder bed pulls the fabric forcibly from behind the needle to produce a clean finish without plyshift. This also prevents seam jamming in cross seam sections of extra-heavy weight fabrics. (Please use a resin roller for easily damageable fabrics such as corduroy.)

Pop-out looper

The looper pops out when the button is pressed so that threading is not wearisome any more.
* Equipped with HR device

- * Stitch length adjustment lever * Differential feed adjustment lever
- * Equipped with sliding binder

Labor saving devices

code	Device names	Descriptions
КН	Flat type vacuum chain cutter	A thread chain is cut as soon as it is sucked up by air suction. There is no need to cut the thrad chain using scissors. The suction inlet is positioned flush with the needle plate and right behind the presser foot. Thanks to this feature, wide double chainstitch, extra heavy weight or woolen thread chains are smoothly sucked up.
PL	Presser foot lifter	Pressing the treadle with your heel raises the presser foot. This device is easy to use, thus decreasing operator fatigue and increasing productivity.
RP	Rear puller	The roller pulls the fabric from behind the needle drop hole. Thanks to this device, the machine smoothly sews difficult-to- feed fabrics, providing beautifully finished products with no plyshifting.
PD	Special mounted table	Special mounted table